

Product Data Sheet

P/N: S+40X

S+40X

Introduction The S+4OX is a market leading industrial safety oxygen sensor, ideal for fixed and portable gas detectors.

Oxygen Sensor (O₂)

Key Features: Resilient to challenging environments, guaranteed life performance, fast response

Performance Characteristics		
Output signal	0.10 ± 0.03 mA	
Zero Current (Offset)	< 0.6% vol. O2 (typically <0.3% vol. O2)	
T90 Response Time	< 10 seconds (typically <5 seconds)	
Measurement Range	0 - 25% Oxygen	
Maximum Overload	30% Oxygen	
Linearity	Linear	
Recommended Load Resistor	100 ohms	


Environmental Details	
Temperature Range Continuous	-30°C to +50°C
Pressure Range	800 to 1200 mbar
Operating Humidity Range	5% to 95% RH

Important Note:

All performance data is based on conditions at 20°C, 50%RH and 1 atm, using DD Scientific recommended circuitry.

Sensor performance is temperature dependent, and please contact DD Scientific for temperature performance other than 20°C.





Product Dimensions
All dimensions in mm
All tolerances ±0.15 mm

iSweek www.isweek.com

Add: 16/F, Bldg. #3, Zhongke Mansion, No.1 Hi-Tech S. Rd, Hi-Tech Park South, Shenzhen, Guangdong, 518067 P.R.China

Tel: + 86-755-83289036 Fax: + 86-755-83289052 E-mail: sales@isweek.com



Output vs Temperature Coefficient Data S+40X Mk III

20

105.0

100.0

95.0

Lifetime Details		
Long Term Output Drift	<5% per annum	
Recommended Storage Temp	0°C to 20°C	
Expected Operating Life	> 24 months in air	
Standard Warranty	24 months from date of dispatch	

Intrinsic Safety Data	
Maximum current in normal operation (pure O2)	0.01 A
Maximum o/c Voltage (10 to 100% O2)	
Maximum s/c Current (10 to 100% O2)	0.5 A

of signal @ 20°C 85.0 -20 -10 10 Temperature °C —Mean —+95% Conf —-95% Conf

Cross Sensitivity Data

Toxic gases at TLV levels will have no cross-sensitivity effect on DD-Scientific oxygen sensors. At very high levels (i.e. percent levels), highly oxidising gases (e.g. ozone, chlorine) will interfere to the extent of their oxygen equivalent, but most other commonly occurring gases will have no effect.

Acid Gases

IMPORTANT NOTE: Acid gases such as CO2 and SO2 will be absorbed by the electrolyte and tend to increase the flux of oxygen to the electrode. This gives an enhanced oxygen signal of approximately 0.3% of signal per 1% CO₂. DD-Scientific oxygen sensors are not suitable for continuous operation in concentrations of CO₂ above 25%.

WARNING: By the nature of the technology used, any electrochemical gas sensor offered by DD Scientific can potentially fail to meet specification without warning. Although DD Scientific Ltd makes every effort to ensure the reliability of our products of this type, where life safety is a performance requirement of the product, we recommend that all sensors and instruments using these sensors are checked for response to gas before use.

Every effort has been made to ensure the accuracy of this document at the time of printing. In accordance with the company's policy of continued product improvement DD SCIENTIFIC Limited reserves the right to make product changes without notice. No liability is accepted for any consequential losses, injury or damage resulting from the use of this document or from any omissions or errors herein. The data is given for guidance only. It does not constitute a specification or an offer for sale. The products are always subject to a program of improvement and testing which may result in some changes in the characteristics quoted. As the products may be used by the client in circumstances beyond the knowledge and control of DD SCIENTIFIC Limited, we cannot give any warranty as to the relevance of these particulars to an application. It is the clients' responsibility to carry out the necessary tests to determine the usefulness of the products and to ensure their safety of operation in a particular application. Performance characteristics on this data sheet outline the performance of newly supplied sensors. Output signal can drift below the lower limit over time.

iSweek www.isweek.com

Add: 16/F, Bldg. #3, Zhongke Mansion, No.1 Hi-Tech S. Rd, Hi-Tech Park South, Shenzhen, Guangdong, 518067 P.R.China

Tel: +86-755-83289036 E-mail: sales@isweek.com Fax: +86-755-83289052