

# **GaN-based UV photodiode**

# Model: GS-ABC-3535LQC

#### **General Features:**

- UVA+UVB+UVC photodiode
- Photovoltaic mode operation
- SMD 3535 ceramic package with quartz window
- Good visible blindness
- High responsivity and low dark current

**Applications:** air purification, water quality measurement






Parameters	Symbol	Value	Unit
Maximum ratings			
Operation temperature range	$T_{opt}$	-25-85	°C
Storage temperature range	$T_{sto}$	-40-85	°C
Soldering temperature (3 s)	T <sub>sol</sub>	260	°C
Reverse voltage	$V_{r\text{-max}}$	-10	V
General characteristics (25 °C)			
Chip size	А	1	mm²
Dark current (V <sub>r</sub> = -1 V)	I <sub>d</sub>	<1	nA
Temperature coefficient	T <sub>c</sub>	-0.02	%/°C
Capacitance (at 0 V and 1 MHz)	Cp	18	pF
Spectral response characteristics (25 °C)			
Wavelength of peak responsivity	λp	355	nm
Peak responsivity (at 355 nm)	R <sub>max</sub>	0.20	A/W
Spectral response range (R=0.1×R <sub>max</sub> )	-	210-370	nm
UV-visible rejection ratio (R <sub>max</sub> /R <sub>400 nm</sub> )	-	>10 <sup>4</sup>	-

### **Spectral response**

#### 0.25 10° 10<sup>-1</sup> 0.20 Responsivity (A/W) 10<sup>-2</sup> 0.15 10 0.10 10⁻ 0.05 10<sup>-4</sup> 250 300 350 400 elenath (nm)

#### Package dimensions




ISweek www.isweek.com

## **GaN-based UV photodiode**

## Model: GS-ABC-3535LQC


#### **Application circuit:**



$$\begin{split} &V_{out}(V) = I_{ph}(A) \times R \; (\Omega) \\ &I_{ph}(A) = R_{\lambda}(A/W) \times A \; (cm^2) \times P \; (W/cm^2) \\ &\text{where A is chip area, P is incident UV power density} \\ &\text{and } R_{\lambda} \; \text{is responsivity at specific wavelength.} \end{split}$$

#### **Evaluation circuit board:**

A small multifunctional amplifier board for developers to simplify and support application development can be separately provided. The evaluation board with one amplifier channel supports both SMD- and TO-type packaged UV photodiodes supplied by GaNo Opto. Users could select one of the two mounting ports for UV photodiode evaluation, while both ports should not be used at the same time.



The evaluation board supports measurement range adjustment function via a dip switch. Different setting of the dip switch corresponds to different load resistance value, which determines the amplification magnitude of the signal processing circuit. A temperature sensor on board is used for embedded temperature compensation.

The UV photodiode evaluation board has both analog and digital output interface. Analog interface provides voltage signal as a function of UV illumination intensity, while digital interface provides serial communication to PC with direct digital output. A backside micro-USB port provides digital interface to PC with USB cable connection. Users could use serial communication host software in PC to receive direct measurement date from the evaluation board.

For ordering this evaluation board, please visit <a href="http://www.gano-opto.com">http://www.gano-opto.com</a>, where the application note of this board, its host software as well as information about GaNo Opto's UV photodiodes can be found.

Note: The board is shipped without any photodiodes.